

Modifications Made to TECLOG2 Software

New Features / Enhancements with Version 2.1.100 (released November 2010)

- TECLOG2 can communicate with up to 16 Energy Conservatory data acquisition devices simultaneously.
- TECLOG2 now contains multi-fan airtightness testing features. For more information, read "Airtightness Testing with TECLOG2.pdf" found under the TECLOG2 help menu.
- TECLOG2 has a new data marking method referred to as Periods of Record (POR). These periods can be defined by graphically selecting a time interval using the Region Select Tool. These POR are an integral part of airtightness testing but are also useful for other general data analyses.
- The text export feature of TECLOG2 is aware of these POR which can help in exporting an organized text version of the data file.
- TECLOG2 has a "Daily File Save" option to automatically create separate data files for each day. This is useful in long term data logging.
- TECLOG2 locates data acquisition devices by serial number rather than by COM port number, simplifying the configuration process. This is especially useful when using several data acquisition devices.
- TECLOG2 works with Windows XP, Vista and Windows 7. For Windows Vista and Windows 7, Winhelp.exe is required to view the built-in help file. For more information, see <http://support.microsoft.com/kb/917607>